


QUICK START
METRON 80 BTC




- 1 Measure button
- 2 Function button
- 3 SET button
- 4 Target point finder camera
- 5 Addition | Up
- 6 Subtraction | Down
- 7 ON/OFF

 **Bluetooth + app**


Use METRON with free SOLA Measures app for smart features: take photos, sketch and dimension distances, save measuring results, manage and share them.


1. Activate Bluetooth on METRON and smartphone.


2. Open SOLA Measures app to connect METRON to your smartphone.




23


  


 1x a + b


 1x a - b

21




 camera


1x  2-zoom


2x  4-zoom




22

SET   

 inclination sensor

 display turns

 1-100 memory





19


SET  

 set distance offset




 timer 5 sec.


20


   




17



SET   


 Bluetooth automatic

 m m/ft/in/”






18

  **S**







15

  **V**






16



13

  **S**



14

Start

2 sec. ON

2 sec. OFF

1

1 x

3

2 sec. continuous

5

→

7

→

9

→

11

SET

2

2 sec. min/max

4

→

6

→

8

→

10

→

12

SOLA-Messwerkzeuge GmbH
 Unteres Tobel 25, 6840 Götztis, Austria
 Tel: +43 (0)5523 53380-0
 sola@sola.at, www.sola.at



Please find the operating instructions on sola.at

Download free **SOLA Measures app** to connect METRON 80 BTC to your smartphone via Bluetooth.

